

REPLACEMENT COMPONENTS - CONSUMABLES

Component	WLCP PN	Frequency of Replacement
15W X UV Lamp Assembly	12-8310	Every 12 months, or as required Factory Part No CT-2085-IA0-00
Hot Tank 120V/500W - 1.6L with Thermistor	10-4029	Replace every 3 to 5 years depending on usage. Factory Part No HT-3024
Sediment Filter - 10" 20 Micron Inline Filter	FT-0053-IL containing FT-0055 Filter Element	Every 12 months or every 1,250 gallons. Factory Part No FT-0053-IL Assembly containing FT-0055-WLT Filter Element
1-micron 10" Inline CBC Filter for CTO, Lead, Cyst and Asbestos Reduction (Carbon Block) NSF 53 Required for NSF Certification	FT-0063-IL containing FT-0064 Filter Element	Every 12 months or every 1,250 gallons. Factory Part No FT-0063-IL Assembly containing FT-0064-WLT Filter Element
10-micron 10" Inline GAC Filter for Taste and Odor Reduction (Grannual Activated Carbon) NSF 42 Required for NSF Certification	FT-0035-IL containing FT-0038 Filter Element	Every 12 months or every 1,250 gallons. Factory Part No FT-0035-IL Assembly containing FT-0038-WLT Filter Element

* One pre-installed. One required for NSF-42 / NSF-53 Certification.

⚠ CAUTION! Use only Waterlogic Replacement parts that can be obtained from *Waterlogic* or an *Authorized Waterlogic Dealer*, failure to do so will void the Warranty.

See Installation and Service Manual for additional information.

Hot Tank Service

Hot Tanks (with controls) must be replaced at least every 3-5 years depending on usage. Descaling hot tank may be required on a regular basis depending upon filtration and local water conditions. See Installation and Service Manual for further details.

Surface Cleaning

Clean on a regular basis with damp lint free cloth. Never use harsh chemicals (alcohol or acid based) or abrasive agents on any part of the product to avoid damage. A mild cleaner such as Simple Green or equivalent is recommended.

DISPOSAL

End of Life


At the **end of this product's life**, ensure that it is disposed of in an environmentally friendly manner which is fully compliant **with all Federal/State/Local Requirements and Guidelines**. Do not dispose of this appliance with normal household or business waste.

WL2FL TOWER LAYOUT DRAWING AND PARTS LIST

Yellow = Consumables

Green = Recommended spare parts



Wetted Parts



No	WLUSA Part Number	Description	Factory Part Number	Stocked?	
Consumables					
1	10-4029	Hot Tank 120V/500W - 1.6L with Thermistor	HT-3024	Yes	
2	12-8310	15W X UV Lamp Assembly	CT-2085-IA0-00	Yes	
3	FT-0035	GAC Filter - 10" Carbon Activated Inline Filter	FT-0035-IL-WLT	Yes	
4	FT-0053	Sediment Filter - 10" Sediment 20 Micron Inline Filter	FT-0053-IL-WLT	Yes	
5	FT-0063	1-micron 10" Inline CBC Filter for CTO, Lead, Cyst and Asbestos Reduction – Carbon Block	FT-0063-WLT	Yes	
Not shown	01-2076	Scale Kleen	NA	Yes	
Recommended Spare Parts					
1.1	12-1360	Overload with Manual reset - 221°F (105°C) <i>Recommend stocking 2 each per 10 units purchased</i>	HT-3012	Yes	
1.2	12-6900	Overload Metal Cover <i>Recommend stocking 2 each per 10 units purchased</i>	ST-8290	Yes	
6	PL-0191-L00-BL	Black Top Cover <i>Recommend stocking 2 each per 10 units purchased</i>	PL-0191-L00-BL	Yes	
7	EN-0008-LA1-00	13W / 15W 120V / 60Hz Electronic FX Ballast <i>Recommend stocking 2 each per 10 units purchased</i>	EN-0008-LA1-00	Yes	
8	PU-4017	Solenoid Valve DC24V 500mm <i>Recommend stocking 2 each per 10 units purchased</i>	PU-4017	Yes	
9	EN-6134	Main PCB <i>Recommend stocking 2 each per 10 units purchased</i>	EN-6134	Yes	
9.1	10-3017	Plastic PCB Support <i>Recommend stocking 2 each per 10 units purchased</i>	EN-6059	Yes	
10	PL-0194-L00-BL	Black Drip Tray Body <i>Recommend stocking 4 each per 10 units purchased</i>	PL-0194-L00-BL	Yes	
11	PL-0195-L00-BL	Black Drip Tray Grill <i>Recommend stocking 4 each per 10 units purchased</i>	PL-01 95-L00-BL	Yes	
12	LP-0422-L00-00	Hot and Cold User Interface Label <i>Recommend stocking 2 each per 10 units purchased</i>	LP-0422-L00-00	Yes	



13	PL-0199-L00-00	Hot and Cold Dispense Silicon Button Mat <i>Recommend stocking 2 each per 10 units purchased</i>	PL-0199-L00-00	Yes	
14	EN-0078-L00-00	Display PCB <i>Recommend stocking 2 each per 10 units purchased</i>	EN-0078-L00-00	Yes	
15	12-8305	Quartz Spiral UV Faucet <i>Recommend stocking 2 each per 10 units purchased</i>	FU-0007	Yes	
16	12-1500	Solenoid Valve DC24V 1000mm <i>Recommend stocking 2 each per 10 units purchased</i>	PU-4016	Yes	
17	12-8370	Hot Water Faucet <i>Recommend stocking 2 each per 10 units purchased</i>	PL-1351	Yes	
17.1	10-3048	Faucet Nipple – Blue with Screen <i>Recommend stocking 2 each per 10 units purchased</i>	PL-1013	Yes	
17.2	10-2600	Silicon Faucet O-ring <i>Recommend stocking 2 each per 10 units purchased</i>	CT-2007	Yes	
Remainder of Parts					
1.2	NA	Hot Tank Thermistor	HT-3002	No	
18	12-8003	Upper Shelf	ST-8136-R2	Yes	
19	12-8375	Transformer 1.6A / 120 V	EL-5147	Yes	
20	Purchase from John Guest	JG Equal Elbow Connector 1/4" John Guest P/N PI0308S	PU-4008	No	
21	12-5245	Main PCB Bracket	ST-8165-CN	Yes	
22	NA	Cold Tank Assembly - 4Liters	CT-2017-A	No	
23	PL-0202-L00-BL	Black Front Top Panel	PL-0202-L00-BL	Yes	
24	PL-0192-L00-SI	Silver Front Top Panel Trim	PL-0192-L00-SI	Yes	

25	EL-0148-L00-00	LED Light Pipe	EL-0148-L00-00	Yes	
26	Purchase from John Guest	JG 3/8" x 1/4" Reducing Elbow (PI211208S)	PU-4137	No	
27	12-8320	Firewall UV Lamp Rubber	CT-2088	Yes	
28	FW-0027	Firewall Mark IV Stainless Assy No internal components	FW-0027-I00-00	Yes	
29	AK-0064	UVC Sensor Assembly	AK-0064	Yes	
30	PL-0197-L00-BL	Black Bottom Front Insert Panel	PL-0197-L00-BL	Yes	
31	PL-0196-L00-SI	Silver Front Panel Trim	PL-0196-L00-SI	Yes	
32	Purchase from John Guest	JG Reducing Elbow Connector 5/16" * 1/4" (PI211008S)	PU-4007	No	
33	Purchase from John Guest	JG Equal Tee Connector 1/4" (PI0208S)	PU-4011	No	
34	CU-0001	Solenoid Cushion	CU-0001	Yes	
35	12-8005	Filter Bracket	ST-8138	Yes	
36	20-1010	2.8" Filter Clip	PU-4161	Yes	
37	10-3083	Unit Rubber Feet	ST-8016	Yes	
38	12-8004	Bottom Tray	ST-8137	Yes	











39	12-3155	Leak Tray	PL-1294-A	Yes	
40	12-3180	Leak Containment Tray Clip (sensor 0.5mm)	ST-8207-CN	Yes	






Verify compressor in machine before ordering parts as the Compressor P/N CO-0020-L00-00 and 10-2200 (CO-0001A) and related parts are not interchangeable.

CO-0020-L00-00 Compressor (WL2FL-FX)

41A.1	CO-0020-L00-00	LG Compressor 120V R134A CSB035LJCM	CO-0020-L00-00	Yes	
41A.2	CO-0019-L00-00	Compressor Capacitor	CO-0019-L00-00	Yes	
41A.3	ST-0216-L00-00	Capacitor Bracket	ST-0216-L00-00	Yes	
41A.4	CO-0017-L00-00	PTC Relay	CO-0017-L00-00	Yes	
41A.5	CO-0018-L00-00	Overload Protector	CO-0018-L00-00	Yes	

CO-0043-I00-00 Compressor (WL2FL-FZ)

41B.1	CO-0043-I00-00	Samsung Compressor (R134a 1/8HP) 120V/60Hz		Yes	
41B.2		Compressor Starter Relay		Yes	
41B.3		Overload Protector		Yes	
41.1	12-1001	Filter Dryer	CO-9008	Yes	
42	10-3067	Bulkhead Union 1/4" x 1/4" John Guest P/N PI1208S	PU-4028	Yes	
43	10-4004	Black Plastic Handle	PL-1120	Yes	
44	ST-0202-L00-BL	Tower Side Panel - Black	ST-0202-L00-BL	Yes	
45	19-1015	Gasket for Power Socket	ST-8052	Yes	
46	19-1090	Power Line Noise Filter, ElectroMagnetic Interference filter (EMI)	EL-5029	Yes	
47	10-3014	Fuse Holder and Fuse 120V / 15A with One Wire	EL-5053	Yes	

47.1	10-3013	Fuse 120V / 15A	EL-5010	Yes	
48	12-5600	Red Heater and Compressor Switch	EL-5019-A	Yes	
49	NA	Tower Back Panel - Black	ST-0203-L00-BL	No	
50	19-1069	Cold Tank Thermostat 3°C (37.4°F)	CT-2070-A	Yes	
50.1	LP-0326	Cold Thermostat Cover Label	LP-0326-L00-00	Yes	
51	12-8102	Wire Condenser	CO-9027	No	
52	Purchase from John Guest	JG LLD PE Tube - Blue O.D.1/4" John Guest P/N PE-08-BI-1000F-B	PU-4031	No	
53	10-7040	Silicon Tube 5/16" for hot water	PL-4064-L00-00	Yes	
Not Shown	10-3007	Power Cord 120V – 18240mm	EL-5001-B	Yes	